



Proof Boxes



ALL SERVICE CONNECTIONS
ARE ON TOP OF PROOF BOX

DO NOT PUT FLOOR
DRAIN UNDER BOX



Model	Rack Cap.	Rack Wide	Rack Deep	A Width	B Depth
1-1-1	1	1	1	3'-6" ²	7'-8" ²
2-2-1 ²	2	2	1	6'-11"	7'-9" ²
3-3-1 ²	3	3	1	10'-1"	7'-9" ²
4-4-1 ²	4	4	1	13'-3"	7'-9" ²
4-2-2 ²	4	2	2	6'-11"	13'-0"
5-5-1 ²	5	5	1	16'-5"	7'-9"
6-3-2 ²	6	3	2	10'-1"	13'-0" ²
6-2-3 ²	6	2	3	6'-11"	19'-6" ²
7-7-1 ²	7	7	1	22'-9"	7'-9" ²
4-4-2 ²	8	4	2	13'-3"	13'-0" ²
9-3-3 ²	9	3	3	10'-1"	19'-6" ²
10-5-2 ²	10	5	2	16'-5"	13'-0" ²
12-4-3 ²	12	4	3	13'-3"	19'-6" ²
12-3-4 ²	12	3	4	10'-1"	25'-4"

- D** Door Opening - 34 x 78
 - E** Sliding doors for access to mechanism
 - F** 1/4 HP 115v. 1 PH Motor
 - G** Cleanout door - Approx 7" above floor
 - H** 110 V. 1 PH. Approx 10 Amps. Connection (30" above floor)
- Connections from ceiling should be stubbed in above oven height



Additional Certifications Required are Responsibility of Owner

